SHELCO MicroVantage™ VGPS Series

Vent Grade Hydrophobic Polysulfone Membrane Filter Cartridge





- Absolute retention ratings at 0.2 micron
- 6.0 square feet (0.56 m2) of media surface area per ten inch length for optimal performance
- Highly tapered asymmetric pore structure provides excellent flow rate and dirt holding capacity
- Cost-effective absolute filtration for vent applications not integrity tested
- Rigid, molded cage protects pleated media and strengthens structural stability
- Manufactured in state-of-the-art white room for high purity
- Complies with Food & Drug Administration's CFR criteria for food & beverage contact.
- Meets USP Class VI Biological Test for plastics
- Available in common and end cap configurations to fit most filter housings
- Produced in standard lengths up to 40 inches

Applications

Tank Ventilation Process Gases Compressed Air

Specifications & Operating Parameters

Pore Sizes 0.2 microns absolute retention

Nominal Lengths 9.75" (24.7 cm), 10" (25.4 cm), 20" (50.8 cm), 30" (76.2 cm), 40" (101.6 cm)

Outside Diameter 2.67" (6.78 cm)

Inside Diameter 1.0" (2.54 cm)

Media Surface Area

6.0 sq.ft. (0.56 m2) per 10 inches filter length

Gaskets/O-rings

Silicone, Buna N, EPR, Viton, Teflon Encapsulated Viton (0-rings only)

Materials of Construction

Filter Media: Hydrophobic Polysulfone

Outer Cage Polypropylene Inner Core: Polypropylene End caps: Polypropylene Maximum Operating Temperature 176°F (80°C)

Recommended Change-out Differential Pressure 35 psid (2.4 bar)

Maximum Differential (Collapse) Pressure

Forward: 75 psid @ 70°F (5.2 bar @ 21° C) Reverse: 40 psid @ 176°F (2.8 bar @ 80° C)


Sanitization and Sterilization

Hot water at 175°F (80°C) at 5 psid for 30 minutes In-line steam at 257°F (125°C) @ 1 psid (0.7 bar) for 30 minutes Autoclavable at 257°F (125°C) for 30 minutes

FDA and USP Compliance

All materials comply with the requirements of Food and Drug Administration Title 21 of The Code of Federal Regulations 174.5, 177.1520 and 177.1630. All components

Flow vs. Pressure Drop



Ordering Guide (Example: VGPS0.2-10S4S)

VGPS	-0.2	10	\$4	- S
PRODUCT CODE	MICRON	LENGTH	END CAP CONFIGURATION	GASKET/O-RING
MAN	0.02	9.75" 10" 19.75" 20" 29.25" 30" 40"	S1 = D0E S3 = 222 w/ Fin End S4 = 222 w/ Flat End S5 = 226 w/ Fin End S6 = 226 w/ Flat End S7 = Internal O-ring with Recessed Plug S9 = Internal O-ring on both ends	B = Buna N E = EPR S = Silicone V = Viton T = Teflon encapsulated Viton (O-ring only)

Filter Housings

Shelco manufactures a full line of filter housings. From our rugged single cartridge housings to our heavy duty multi-cartridge housings, Shelco is the perfect choice for your filtration solutions.



Filter Products Company

5220 Klockner Dr. Richmond, VA 23231 USA

Tel: 1 (800) 726-5515 / E-mail: info@filterproducts.com